



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 76 A, Number of poles: 3, Pitch in mm (P): 6.00, Insulated: No, Width: 29.8 mm
Order No.	0470800000
Type	QL 3 SAK16
GTIN (EAN)	4008190011574
Qty.	50 items

QL 3 SAK16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	29.8 mm	Width (inches)	1.1732 inch
Net weight	2.48 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Cu Zn Colour grey

System specifications

Version for cross-connection link

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
Explosion-tested version No

Dimensions

Pitch in mm (P) 6.00 mm

General

Number of poles 3 Installation advice Direct mounting

Rating data

Nominal current 76 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		