

## DEK 5 FW 251-300

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a large range of ready-printed markers. Strips for fast installation in one work step. The printing is easy to read, rich in contrast, and is available in five widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank cards, MultiCard or as cards with standard printing

### General ordering data

|            |  |
|------------|--|
| Version    | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, white |
| Order No.  | <a href="#">0473460251</a>   |
| Type       | DEK 5 FW 251-300   |
| GTIN (EAN) | 4008190123529  |
| Qty.       | 500 items  |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 5 mm   | Width (inches)  | 0.1968 inch |
| Net weight | 0.04 g |                 |             |

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2 eq. |  |

**General data**

|  |                          |      |  |
|--|--------------------------|------|--|
| Material colour according to resistance code | 9                        |      |  |
| Orientation of print                         | horizontal               |      |  |
| Printing method                              | MC Laser                 |      |  |
| Width  | 5 mm                     |      |  |
| UL 94 flammability rating                    | V-2                      |      |  |
| Operating temperature range, max.            | 100 °C                   |      |  |
| Operating temperature range, min.            | -40 °C                   |      |  |
| Colour                                       | white                    |      |  |
| Halogen                                      | No                       |      |  |
| Basic material                               | Polyamide 66             |      |  |
| Colour of printing                           | black                    |      |  |
| Printed characters                           | Numbers                  |      |  |
| Number of markers per packaging unit         | Form of supply           | Card |  |
| Number of markers per combination            | 1 Card = Terminal marker |      |  |
| Operating temperature range                  | -40...100 °C             |      |  |
| Application/manufacturer                     | Weidmueller              |      |  |

**Connector markers**

Pitch in mm (P) 5.00 mm

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |