

## IK 4 GG ZB4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

### General ordering data

Version	Cover hood (terminal), Polyamide 66
Order No.	<a href="#">0475460000</a>
Type	IK 4 GG ZB4
GTIN (EAN)	4008 190065348
Qty.	50 items

## IK 4 GG ZB4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	14.5 mm	Depth (inches)	0.5709 inch
Height	19 mm	Height (inches)	0.748 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	0.96 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Polyamide 66	Insulating material	PA
Colour	silver	UL 94 flammability rating	V-2

### System specifications

Version	for busbar 10 x 3 mm
---------	----------------------

### Additional technical data

Installation advice	Busbar
---------------------	--------

### Dimensions

TS 35 offset	39 mm
--------------	-------

### General

Installation advice	Busbar	Operating temperature range, max.	100 °C
---------------------	--------	-----------------------------------	--------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		