


ADP 3/HP3 1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Similar to illustration

Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	SAK Series, Cover profile, Transparent, 1000 mm
Order No.	0485400000
Type	ADP 3/HP3 1M
GTIN (EAN)	4008 190023928
Qty.	20 M

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	89 mm	Depth (inches)	3.5039 inch
Height	34.5 mm	Height (inches)	1.3583 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	287 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PVC	Colour	Transparent
UL 94 flammability rating	V-2		

System specifications

Version	cover plate
---------	-------------

Additional technical data

Snap-on	Yes	Installation advice	Direct mounting
---------	-----	---------------------	-----------------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Drawings

