

SH 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	Busbar support, medium yellow, 130 °C, Width: 40 mm, V-0, KrG, when screwed in
Order No.	0494920000
Type	SH 2
GTIN (EAN)	4008190007584
Qty.	10 items

SH 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	40 mm	Width (inches)	1.5748 inch
Net weight	22.1 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Mounting rail

Surface finish	all others	Basic material	KrG
----------------	------------	----------------	-----

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		