

**VP 29-K54****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, PG 29, 8 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	<a href="#">0501160000</a>
Type	VP 29-K54
GTIN (EAN)	4008190174361
Qty.	25 items

## VP 29-K54

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	3.5 mm	Height (inches)	0.1378 inch
Length	11.5 mm	Length (inches)	0.4528 inch
Diameter	37 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	7 mm	Net weight	5.12 g

### Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General information

Head diameter	44.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Protection degree	IP54	Cable gland	PG
Basic material	Polyamid 6 (PA6 - GF30)	Diameter of sealing ring	37.00 mm
External thread	PG 29	Length of thread	8 mm

### Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

