

VP 36-K54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK (blanking plug in plastic), Blanking plug, in closed state, PG 36, 10 mm, IP65, Polyamid 6 (PA6 - GF30)
Order No.	0501260000
Type	VP 36-K54
GTIN (EAN)	4008 190020972
Qty.	10 items

VP 36-K54

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	4 mm	Height (inches)	0.1575 inch
Length	14 mm	Length (inches)	0.5512 inch
Diameter	47 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	9 mm	Net weight	10.4 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Head diameter	55.00 mm	Protection degree with GWDR	IP65
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Halogen	No
Protection degree	IP54	Cable gland	PG
Basic material	Polyamid 6 (PA6 - GF30)	Diameter of sealing ring	47.00 mm
External thread	PG 36	Length of thread	10 mm

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

