

## CLI RH 20-10 CLI R 10

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

### General ordering data

Version	CableLine, Mounting mandrel holder
Order No.	<a href="#">0563600000</a>
Type	CLI RH 20-10 CLI R 10
GTIN (EAN)	4008 1900 18436
Qty.	1 items

**CLI RH 20-10 CLI R 10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	28 mm	Depth (inches)	1.1024 inch
Height	55 mm	Height (inches)	2.1654 inch
Width	55 mm	Width (inches)	2.1654 inch
Net weight	42.5 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Material colour according to resistance code	6	Width	55 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Colour	blue
Halogen	Yes	Basic material	Polyamide
Recommended industries	Process, Machinery	Operating temperature range	-40...100 °C

**Conductor and cable markers**

Halogen	Yes
---------	-----

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Example of use**

---

