

CLI RH 20-02 CLI R 02

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Version	CableLine, Mounting mandrel holder
Order No.	0563700000
Type	CLI RH 20-02 CLI R 02
GTIN (EAN)	4008 19029 1136
Qty.	1 items

Technical data

Dimensions and weights

Depth	28 mm	Depth (inches)	1.1024 inch
Height	55 mm	Height (inches)	2.1654 inch
Width	55 mm	Width (inches)	2.1654 inch
Net weight	41.5 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	2	Width	55 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Colour	red
Halogen	Yes	Basic material	Polyamide
Recommended industries	Process, Machinery	Operating temperature range	-40...100 °C

Conductor and cable markers

Halogen	Yes
---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Example of use

