



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 12 mm, green
Order No.	<a href="#">0565900000</a>
Type	H16,0/22 GN
GTIN (EAN)	4008 190022 18 1
Qty.	100 items
Packaging	loose

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E499744

**Dimensions and weights**

Net weight	0.53 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	Wire end ferrule with plastic collar, green	Version	Standard
------------------------	---	---------	----------

**Wire-end ferrules**

Contact surface diameter (D1)	5.8 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	8.8 mm	Plastic collar thickness (S2)	0.4 mm
L1 in mm	22.00 mm	Wire connection cross section AWG, max.	AWG 6
Metal sleeve thickness (S1)	0.2 mm	Stripping length	15 mm
Conductor cross-section	16 mm <sup>2</sup>	Colour code	Weidmueller

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

