

CLI R 1-3 GE/SW P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Version	CableLine, Mounting mandrel
Order No.	0572901668
Type	CLI R 1-3 GE/SW P
GTIN (EAN)	4008 190079833
Qty.	10 items

CLI R 1-3 GE/SW P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	3 mm	Height (inches)	0.1181 inch
Width	4.2 mm	Width (inches)	0.1654 inch
Net weight	2.3 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4	Orientation of print	horizontal
Type of printing	Standard	Printing method	hot-embossing
Version	MultiPack	Width	4.2 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Colour	yellow
Halogen	Yes	Basic material	PVC, soft, without Cadmium
Colour of printing	black	Printed characters	Upper-case letters
Recommended industries	Process, Machinery	Number per mandrel	25
Operating temperature range	-30...80 °C	Imprint	P

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	4 mm ²
Conductor cross-section, min.	1.5 mm ²	Conductor O.D., max.	5 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 5 mm
Cross-section for connected wire	1.5 - 4 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		