

SKH F32 (Z&D) LP RH2

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Plug-in card holders are used to adapt cards from the Euro format (19") to connectors in compliance with IEC 603/DIN 41612 and DIN 41617.

Plug-in card holders consist of the following components:

- Circuit board with standard connectors and inserts with clamping-yoke connection.
- Flange housing and holder/pull-out mechanism for the circuit card.
- Plug-in card and mounting foot for attaching to mounting rail or directly to panel.

The plug-in card holders are normally used in the following cases:

- For quick adaptation in industrial applications of different 19" modules, and for avoiding the expense of a 19" rack.
- When there are only a few cards to install and connect.
- The circuit board is located in a remote position where the cabling cannot be easily handled.
- An older system needs to be updated with additional electronics modules.
- For test devices, production processes and laboratories: where circuit boards needs to be swapped out quickly and connections must be easy to handle.

General ordering data

Version	Interface, Plug-in connector, acc. to DIN 41612 female, 32F
Order No.	0586961001
Type	SKH F32 (Z&D) LP RH2
GTIN (EAN)	4032248046256
Qty.	1 items

SKH F32 (Z&D) LP RH2

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



RoHS Conform

Dimensions and weights

Depth	144 mm	Depth (inches)	5.6693 inch
Height	51 mm	Height (inches)	2.0079 inch
Width	131 mm	Width (inches)	5.1575 inch
Net weight	200 g		

Temperatures

Storage temperature -40...60 °C Operating temperature 0...55 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Connection data

Number of poles (control side)	32-pole female	Type (control side)	32F
Connection (field side)	LP 5.08mm	Contact assembly	z and d
Design of the pluggable board	100x160 mm euro format for 19" racks	Connection on control side	Plug-in connector, acc. to DIN 41612 female

Rating data

Rated voltage 250 V UC Rated current per connection 4 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	250 V
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1.2/50μs)	2.1 kV	Insulation test voltage AC	1.2 kV

Connection field

Min. wire cross-section, AWG	AWG 26	Type of connection	Screw connection
Sleeve with plastic collar, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible, max. H05(07) V-K	4 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Clamping range, max.	6 mm ²	Clamping range, min.	0.5 mm ²
Max. wire cross-section, AWG	AWG 12		

Standard features

Design IEC603 F32

SKH F32 (Z&D) LP RH2

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Technical data**Classifications**

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

SKH F32 (Z&D) LP RH2

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

SKH F32 (Z&D) LP RH2

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 35X7.5 2M/ST/ZN	Version
Order No.	0383400000	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190088026	Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Qty.	40 M	
Type	TS 35X15/2.3 2M/ST/ZN	Version
Order No.	0498000000	Terminal rail, Accessories, Steel, galvanic zinc plated and passivated,
GTIN (EAN)	4008190042493	Width: 2000 mm, Height: 35 mm, Depth: 15 mm
Qty.	20 M	

Accessories

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Type	FM 4/TS35	Version
Order No.	0687900000	Mounting foot on mounting rail, silver, Steel, bright finish, M 4, Width:
GTIN (EAN)	4008190086459	14 mm
Qty.	40 ST	