

KLBU SH1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, Clamping yoke for shield connection
Order No.	0635960000
Type	KLBU SH1
GTIN (EAN)	4008 190007 140
Qty.	20 items

KLBUE SH1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	26.5 mm	Height (inches)	1.0433 inch
Width	15 mm	Width (inches)	0.5906 inch
Net weight	1.69 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.214 kg CO2 eq.	

Material data

Colour	dark beige	UL 94 flammability rating	V-2
--------	------------	---------------------------	-----

System specifications

Version	For the rail holder	End cover plate required	No
Mounting rail	TS 35		

Additional technical data

Type of fixing	Snap-on	Installation advice	Direct mounting, Busbar
Explosion-tested version	No		

Conductors for clamping (rated connection)

Type of connection	Spring contact
--------------------	----------------

Dimensions

Pitch in mm (P)	16.00 mm
-----------------	----------

General

Installation advice	Direct mounting, Busbar	Mounting rail	TS 35
---------------------	-------------------------	---------------	-------

Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		