


CLI O 20-3 GE/SW 9 MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm² to max. 4.0 mm². The shape and design guarantee secure and permanent attachment of the individually combinable markers. Advantages:

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 3 - 4 mm, 3 x 5.5 mm, yellow |
| Order No. | 0648 101529 |
| Type | CLI O 20-3 GE/SW 9 MP |
| GTIN (EAN) | 4008 190143923 |
| Qty. | 200 items |

CLI O 20-3 GE/SW 9 MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 5 mm | Depth (inches) | 0.1968 inch |
| Height | 3 mm | Height (inches) | 0.1181 inch |
| Width | 5.5 mm | Width (inches) | 0.2165 inch |
| Net weight | 0.04 g | | |

Temperatures

Operating temperature range -30...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|--|--------------------|-----------------------------------|----------------------------|
| Material colour according to resistance code | 4 | Orientation of print | horizontal |
| Type of printing | Standard | Printing method | hot-embossing |
| Version | MultiPack | Width | 5.5 mm |
| UL 94 flammability rating | V-0 | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Colour | yellow |
| Halogen | Yes | Basic material | PVC, soft, without Cadmium |
| Colour of printing | black | Printed characters | Numbers |
| Recommended industries | Process, Machinery | Operating temperature range | -30...80 °C |
| Imprint | 9 | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | Yes | Conductor cross-section, max. | 3 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Conductor O.D., max. | 4 mm |
| Conductor O.D., min. | 3 mm | Conductor O.D. | 3 - 4 mm |
| Cross-section for connected wire | 1.5 - 3 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings



Similar to illustration