

## CLI RS 5 MDCLI C 1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

### General ordering data

|            |                             |
|------------|-----------------------------|
| Version    | CableLine, Mounting mandrel |
| Order No.  | <a href="#">0648300000</a>  |
| Type       | CLI RS 5 MDCLI C 1          |
| GTIN (EAN) | 4008 1900 10546             |
| Qty.       | 1 items                     |

## CLI RS 5 MDCLI C 1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5 mm   | Depth (inches)  | 0.1968 inch |
| Height     | 100 mm | Height (inches) | 3.937 inch  |
| Width      | 5 mm   | Width (inches)  | 0.1968 inch |
| Length     | 100 mm | Length (inches) | 3.937 inch  |
| Net weight | 9.68 g |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected                         |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 70267faf-4457-48b8-92bf-2799db2a9227 |

### General data

|                                   |             |                                   |                    |
|-----------------------------------|-------------|-----------------------------------|--------------------|
| Type of printing                  | Standard    | Version                           | MultiPack          |
| Width                             | 5 mm        | UL 94 flammability rating         | V-0                |
| Operating temperature range, max. | 80 °C       | Operating temperature range, min. | -30 °C             |
| Colour                            | silver      | Halogen                           | Yes                |
| Length                            | 100 mm      | Basic material                    | Steel              |
| Printed characters                | Numbers     | Recommended industries            | Process, Machinery |
| Operating temperature range       | -30...80 °C |                                   |                    |

### Conductor and cable markers

|                                  |                           |                               |                     |
|----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen                          | Yes                       | Conductor cross-section, max. | 4.5 mm <sup>2</sup> |
| Conductor cross-section, min.    | 1.5 mm <sup>2</sup>       | Conductor O.D., max.          | 5.5 mm              |
| Conductor O.D., min.             | 2.5 mm                    | Conductor O.D.                | 2.5 - 5.5 mm        |
| Cross-section for connected wire | 1.5 - 4.5 mm <sup>2</sup> |                               |                     |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Drawings**

**Example of use**

---

