

CLI RS 5 MDCLI C 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Version	CableLine, Mounting mandrel
Order No.	0648300000
Type	CLI RS 5 MDCLI C 1
GTIN (EAN)	4008 1900 10546
Qty.	1 items

CLI RS 5 MDCLI C 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	5 mm	Depth (inches)	0.1968 inch
Height	100 mm	Height (inches)	3.937 inch
Width	5 mm	Width (inches)	0.1968 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	9.68 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	70267faf-4457-48b8-92bf-2799db2a9227

General data

Type of printing	Standard	Version	MultiPack
Width	5 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Colour	silver	Halogen	Yes
Length	100 mm	Basic material	Steel
Printed characters	Numbers	Recommended industries	Process, Machinery
Operating temperature range	-30...80 °C		

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	4.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Conductor O.D., max.	5.5 mm
Conductor O.D., min.	2.5 mm	Conductor O.D.	2.5 - 5.5 mm
Cross-section for connected wire	1.5 - 4.5 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

Example of use

