Data sheet

# KSP L80 S

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

| | |
|---|---|
| Version | KSP (Klippon shroud), Protective cap, Silicone |
| Order No. | 0930700007 |
| Type | KSP L80 S |
| GTIN (EAN) | 4032248976027 |
| Qty. | 10 items |
| Delivery status | Discontinued |
| Available until | 2023-07-30T00:00:00+02:00 |

# Data sheet

## KSP L80 S

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Height | 120 mm | Height (inches) | 4.7244 inch |
| Length | 150 mm | Length (inches) | 5.9055 inch |
| Net weight | 54.6 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature | -60 °C...200 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General information

| | | | |
|---|---|---|---|
| Silicone | Yes | O.D. | 84 mm |
| Operating temperature range, max. | 200 °C | Operating temperature range, min. | -60 °C |
| Halogen | halogen-free | Thickness | 2.00 mm |
| Basic material | Silicone | Inside diameter D2 | 80.00 mm |
| Gap, internal dimension B | 85.00 mm | Hardness (IRHD) | 60 |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |

# KSP L80 S

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

