

KSWN M20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSWN (flat gasket - nylon), Sealing ring, M 20, Nylon 6
Order No.	0930730002
Type	KSWN M20
GTIN (EAN)	4032248849802
Qty.	25 items

KSWN M20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	2 mm	Height (inches)	0.0787 inch
Net weight	0.76 g		

Temperatures

Operating temperature -40 °C...135 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
Operating temperature range, max.	135 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Cable gland	M 20
Basic material	Nylon 6	Diameter of sealing ring	29.40 mm
External thread	M 20	Internal thread	M 20

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

KSWN M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

