

LM MT300 89/34 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

| | |
|------------|--|
| Version | LaserMark, Device markers, 34 x 89 mm, white |
| Order No. | 1003400000 |
| Type | LM MT300 89/34 WS |
| GTIN (EAN) | 4032248699292 |
| Qty. | 10 items |

LM MT300 89/34 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 34 mm | Height (inches) | 1.3386 inch |
| Width | 89 mm | Width (inches) | 3.5039 inch |
| Net weight | 11.5 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|--|---|-------------|--|
| Adhesive | Acrylate adhesive | | |
| Material colour according to resistance code | 9 | | |
| Number per sheet | 16 | | |
| Printing method | Laser print | | |
| Version | Self-adhesive | | |
| Width | 89 mm | | |
| UL 94 flammability rating | HB | | |
| Operating temperature range, max. | 150 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | No | | |
| Basic material | Polyester, PVC-free | | |
| Printed characters | without | | |
| Number of markers per packaging unit | 160 | | |
| Number of markers per packaging unit | Form of supply | Label sheet | |
| | Number of combinations per packaging unit | 10 | |
| | Number of markers per combination | 16 | |
| Approval acc. to UL 969 | Yes | | |
| Number of markers per combination | 1 Label sheet = 16 Device markers | | |
| Operating temperature range | -40...150 °C | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

