

## THM WO T 24.5/62 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 6.1 - 13.7 mm, 24.5 x 62 mm, white
Order No.	<a href="#">1003420000</a>
Type	THM WO T 24.5/62 WS
GTIN (EAN)	4032248699315
Qty.	1 items

## THM WO T 24.5/62 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	24.5 mm	Height (inches)	0.9646 inch
Width	62 mm	Width (inches)	2.4409 inch
Net weight	603 g		

### Temperatures

Operating temperature range	-40...107 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Polyacrylate adhesive	
Material colour according to resistance code	9	
Type of printing	neutral	
Version	Self-adhesive	
Width	62 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	107 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	Yes	
Basic material	Tedlar polyvinyl fluoride film®	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Size of labelling field	25 x 24.5 mm	
Approval acc. to UL 969	No	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Conductor and cable markers	
Operating temperature range	-40...107 °C	
Number per roll	2500	

### Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	95 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	13.7 mm
Conductor O.D., min.	6.1 mm	Text field width	24.5 mm
Text field height	25 mm	Conductor O.D.	6.1 - 13.7 mm
Cross-section for connected wire	0.75 - 95 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

