

**SIHA 3/G20/LD 10-36V BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

**General ordering data**

Version	Fuse holder for feed-through modular terminal, blue, 2.31 A, pluggable, V-0, Wemid
Order No.	<a href="#">1005250000</a>
Type	SIHA 3/G20/LD 10-36V BL
GTIN (EAN)	4032248712038
Qty.	25 items

## SIHA 3/G20/LD 10-36V BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	63.1 mm	Depth (inches)	2.4842 inch
Height	39.38 mm	Height (inches)	1.5504 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	8.56 g		

### Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	blue
UL 94 flammability rating	V-0		

### System specifications

Version	Fuse cartridge
---------	----------------

### Additional technical data

Installation advice	Operating instructions/ catalogue	Type of mounting	Plugged
---------------------	--------------------------------------	------------------	---------

### General

Installation advice	Operating instructions/ catalogue	Operating temperature range, max.	120 °C
---------------------	--------------------------------------	-----------------------------------	--------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

**SIHA 3/G20/LD 10-36V BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

