

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Y connector, M12
Order No.	1009370000
Type	SAI-T-5S-PARA
GTIN (EAN)	4032248713622
Qty.	1 items

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 24.64 g

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	4060c755-8d0b-4d43-bdb3-4ffabe9d7497

Connection data

Group outlet - plug-in connector	M12 socket	Single outlet 1 - plug-in connector	M12 socket
Single outlet 2 - plug-in connector	M12 pin	Tightening torque	M12: 0.8 - 1.2 Nm

Technical data customisable plug-in connectors

Number of poles	5	Coding	A-coded
Contact surface	Gold-plated	Contact material	CuSn
Nominal voltage	60 V	Nominal current	4 A
Protection degree	IP67	Pollution severity	3
Cable gland	M 12	Temperature range of housing	-25...+85 °C

Standards

Connector standard IEC 61076-2-101

General data

Number of poles	5	Coding	A-coded
Connection thread	M12	Contact surface	Gold-plated
Contact material	CuSn	Nominal voltage	60 V
Nominal current	4 A	Protection degree	IP67
Pollution severity	3	Cable gland	M 12
Connection 1	M12/M12	Connection 2	Screw
Temperature range of housing	-25...+85 °C	Conductor O.D.	-

Classifications

ETIM 8.0	EC002925	ETIM 9.0	EC002925
ETIM 10.0	EC002925	ECLASS 14.0	27-44-01-06
ECLASS 15.0	27-44-01-06		

SAI-T-5S-PARA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram

