

## IE-PS-V14M-RJ45-FH-P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



PushPull plug-in connector set according to IEC  
61076-3-117 ver.14 (PROFINET), metal incl. RJ45 insert

### General ordering data

Version	Plug insert RJ45 tool-free, Variant 14 metal, Cat.5 (ISO/IEC 11801)
Order No.	<a href="#">1012170000</a>
Type	IE-PS-V14M-RJ45-FH-P
GTIN (EAN)	4032248719815
Qty.	10 items

## IE-PS-V14M-RJ45-FH-P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E316369

### Dimensions and weights

Net weight	69.77 g
------------	---------

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

### General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Variant 14 metal	Wiring	PROFINET
Colour	black	Housing main material	Zinc diecast
Insulation cross-section, min.	0.85 mm	Insulation cross-section, max.	1.6 mm
Category	Cat.5 (ISO/IEC 11801)	Contact surface	Gold over nickel
Connection diameter, solid	0.4...0.64 mm	Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22
Conductor connection cross-section, solid	0.13...0.32 mm <sup>2</sup>	Connection diameter, flexible	0.48...0.76 mm
Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22	Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>
Conductor connection cross-section, flexible	0.14...0.35 mm <sup>2</sup>	MICE classification M	M3
MICE classification I	I3	MICE classification C	C1
MICE classification E	E3	Sheath diameter, min.	5 mm
Sheath diameter, max.	10 mm	Shielding	360°deg; all-round enclosure
Protection degree	IP67	Plugging cycles	750
Ability to reconnect	≥ 10 cycles (for the same or larger cross-section)		

### Electrical properties

Dielectric strength, contact / shield	≥ 1500 V AC/DC	Dielectric strength, contact / contact	≥ 1000 V AC/DC
---------------------------------------	----------------	--	----------------

### General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 60603-7-51	Application-specific communication cable facilities	PROFINET installation instructions
Certificate no. (cULus)	E316369		

Creation date 30.06.2026 07:15:07 MEZ

Catalogue status / Drawings

## IE-PS-V14M-RJ45-FH-P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		


**IE-PS-V14M-RJ45-FH-P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

**Dimensioned drawing**



**Printing**



## IE-PS-V14M-RJ45-FH-P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Dust caps



For protecting your devices against dust and dirt.

### General ordering data

Type	IE-PP-V14P	Version	
Order No.	<a href="#">1058280000</a>	Plug housing protective cap	
GTIN (EAN)	4032248799374		
Qty.	10 ST		

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	ESG 9/11 K MC NE WS	Version	
Order No.	<a href="#">1857440000</a>	ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive	
GTIN (EAN)	4032248402731		
Qty.	200 ST		

