

## IE-PH-V01P-BP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Bayonet plug-in connectors according to IEC  
61076-3-106 ver.1 (EtherNet/IP), plastic, empty housing

### General ordering data

Version	Empty enclosure, Plug housing, bending protection, IP67
Order No.	<a href="#">1012460000</a>
Type	IE-PH-V01P-BP
GTIN (EAN)	4032248720118
Qty.	10 items

## IE-PH-V01P-BP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	126	Depth (inches)	4.9606 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	32 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...70
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	11b17e97-f803-4c09-9278-b20f22f15f81

## General data

Colour	Miscellaneous	Housing main material	PA UL 94 V0
Protection degree	IP67	Plugging cycles	750
Composition	Plug housing with labelling/marketing holder: 9*11 mm; suitable for holding RJ45 and fibre-optic inserts		

## General standards

Connector standard	IEC 61076-3-106 Var. 1
--------------------	------------------------

## Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

**Drawings**

**Dimensioned drawing**

