

**HDC CM BUS SV GCA M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The ConCept-CSB module is a double module and takes up two slots in the ConCept module frame. The ConCept-CSB module consists of a module carrier that is capable of holding two contact carriers. The contact carrier is manufactured with a die-cast zinc alloy which provides it with excellent shielding capabilities. The crimp contacts are insulated from the contact carrier and mounted in a plastic insert. A variety of pole counts – 1, 4 and 8 poles – are available to ensure compatibility with a wide range of applications.

**General ordering data**

|            |   |
|------------|---|
| Version    | Heavy-duty connectors, HDC insert, ConCept module |
| Order No.  | <a href="#">1014080000</a>                        |
| Type       | HDC CM BUS SV GCA M                               |
| GTIN (EAN) | 4032248722624                                     |
| Qty.       | 1 items   |

## HDC CM BUS SV GCA M

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 33.5 mm | Depth (inches)  | 1.3189 inch |
| Height     | 3.9 mm  | Height (inches) | 0.1535 inch |
| Width      | 21.5 mm | Width (inches)  | 0.8465 inch |
| Length     | 33.5 mm | Length (inches) | 1.3189 inch |
| Net weight | 9 g     |                 |             |

## Temperatures

Limit temperature -40 °C ... 70 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## ConCept Pneumatic module

UL 94 flammability rating V-0 Colour Silver grey

## Dimensions

Width 21.5 mm Total length base 33.5 mm  
Height of plug 3.9 mm

## General data

|                               |               |                                      |                        |
|-------------------------------|---------------|--------------------------------------|------------------------|
| Number of poles               | 0             | Type of connection                   | without                |
| UL 94 flammability rating     | V-0           | Colour                               | Silver grey            |
| Plugging cycles               | ≥ 500         | Type                                 | Earth connection clamp |
| Basic material                | Polycarbonate | Series                               | ConCept module         |
| Rated voltage (DIN EN 61984)  | 0 V           | Rated impulse voltage (DIN EN 61984) | 0 kV                   |
| Rated current (DIN EN 61984)  | 0 A           | Free from halogens                   | false                  |
| Low smoke acc. DIN EN 45545-2 | Yes           |                                      |                        |

## Version

Type of connection without Conductor cross-section, max. 0 mm<sup>2</sup>  
Conductor cross-section, min. 0 mm<sup>2</sup> Basic material Polycarbonate

## Classifications

ETIM 8.0 EC000438 ETIM 9.0 EC000438  
ETIM 10.0 EC000438 ECLASS 14.0 27-44-02-18  
ECLASS 15.0 27-44-02-18