



**RF 108 OR****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

**General ordering data**

|            |   |
|------------|---|
| Version    | Clip-in foot, RS 80, RS 90, RS 100 orange, Clip-in foot, Width: 17.5 mm |
| Order No.  | <a href="#">1020690000</a>  |
| Type       | RF 108 OR   |
| GTIN (EAN) | 4032248740154   |
| Qty.       | 20 items  |

## RF 108 OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 26.8 mm  | Depth (inches)  | 1.0551 inch |
| Height     | 107.2 mm | Height (inches) | 4.2205 inch |
| Width      | 17.5 mm  | Width (inches)  | 0.689 inch  |
| Net weight | 8.15 g   |                 |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                                  |           |                     |         |
|----------------------------------|-----------|---------------------|---------|
| UL 94 flammability rating        | V-0       | Insulating material | PA 66/6 |
| Surface finish                   | untreated | Basic material      | PA 66   |
| Comparative Tracking Index (CTI) | 600 ≤ CTI |                     |         |

## General data

|                        |          |                      |      |
|------------------------|----------|----------------------|------|
| Colour                 | orange   | Protection degree    | IP00 |
| Colour chart (similar) | RAL 2000 | Encapsulation option | No   |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 7.0    | EC002779    | ETIM 8.0    | EC002779    |
| ETIM 9.0    | EC002779    | ETIM 10.0   | EC002779    |
| ECLASS 11.0 | 27-18-27-92 | ECLASS 12.0 | 27-18-27-92 |
| ECLASS 13.0 | 27-19-06-05 | ECLASS 14.0 | 27-19-06-05 |
| ECLASS 15.0 | 27-19-06-05 |             |             |