

IE-OP-V04P-1S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Junction box, design for PushPull plug-in connectors ver.4
according to IEC 61076-3-106, plastic

General ordering data

Version	Wall-mounted junction box, IP67, Variant 4 to IEC 61076-3-106
Order No.	1045780000
Type	IE-OP-V04P-1S
GTIN (EAN)	4032248779963
Qty.	10 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	106.9 mm	Depth (inches)	4.2087 inch
Height	61.6 mm	Height (inches)	2.4252 inch
Width	41.8 mm	Width (inches)	1.6457 inch
Net weight	6.5 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

UL 94 flammability rating	V-0	Colour	black
Housing main material	PA	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Protection degree	IP67	Plugging cycles	750

General standards

Connector standard	IEC 61076-3-106 Var. 4
--------------------	------------------------

Classifications

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		

Drawings

Dimensioned drawing

