


IE-CC-V04P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-106 ver.4 (IEC24702), plastic, empty housing

General ordering data

Version	Coupling, IP67, Variant 4 to IEC 61076-3-106
Order No.	1045960000
Type	IE-CC-V04P
GTIN (EAN)	4032248781072
Qty.	10 items

IE-CC-V04P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	109.3 mm	Depth (inches)	4.3031 inch
Height	41.8 mm	Height (inches)	1.6457 inch
Width	41.8 mm	Width (inches)	1.6457 inch
Net weight	5.1 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

UL 94 flammability rating	V-0	Colour	black
Housing main material	PA UL 94 V0	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Protection degree	IP67	Plugging cycles	750

General standards

Connector standard	IEC 61076-3-106 Var. 4
--------------------	------------------------

Classifications

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		

Drawings

Dimensioned drawing

