

IE-BHC-V14M-RJA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-117 ver.14 (PROFINET), metal, RJ45 empty
housing

General ordering data

Version	Empty enclosure
Order No.	1047950000
Type	IE-BHC-V14M-RJA
GTIN (EAN)	4032248784493
Qty.	10 items

IE-BHC-V14M-RJA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Depth	34.7 mm	Depth (inches)	1.3661 inch
Height	39.6 mm	Height (inches)	1.5591 inch
Width	39.6 mm	Width (inches)	1.5591 inch
Net weight	4.95 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

General data

Colour	Miscellaneous	Housing main material	Zinc diecast
Protection degree	IP67	Plugging cycles	750
Composition	Plug housing with labelling tag holder: 9*11 mm; suitable for holding RJ45 and fibre-optic inserts		

General standards

Connector standard	IEC 61076-3-117 Var. 14	Certificate no. (cULus)	E316369
--------------------	-------------------------	-------------------------	---------

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Installation cut-out

