

IE-BSS-V14M-SCRJ-MM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-117 ver.14 (PROFINET), metal incl. SC insert

General ordering data

Version	Flange FO, IP67, Variant 14 standardized flange, SCRJ Duplex coupling, Multimode, POF
Order No.	1058120000
Type	IE-BSS-V14M-SCRJ-MM-C
GTIN (EAN)	4032248799237
Qty.	10 items

IE-BSS-V14M-SCRJ-MM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
 UL File Number Search [UL Website](#)
 Certificate no. (cULus) E316369

Dimensions and weights

Depth	36.15 mm	Depth (inches)	1.4232 inch
Height	42 mm	Height (inches)	1.6535 inch
Width	22.2 mm	Width (inches)	0.874 inch
Net weight	26.86 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Description of article	Variant 14 standardized flange, SCRJ Duplex coupling	Colour	Miscellaneous
Housing main material	Zinc diecast	Type of mounting	2 screws
Protection degree	IP67	Plugging cycles	500
Fibre type	Multimode, POF	Insertion loss	≤ 0.4 dB
Connection 1	SCRJ	Connection 2	SCRJ
Return loss (attenuation)	≥ 30 dB		

General standards

Connector standard	IEC 61076-3-117 Var. 14, IEC 61754-24	Certificate no. (cULus)	E316369
--------------------	---------------------------------------	-------------------------	---------

Classifications

ETIM 8.0	EC000752	ETIM 9.0	EC000752
ETIM 10.0	EC000752	ECLASS 14.0	19-17-01-16
ECLASS 15.0	19-17-01-16		

IE-BSS-V14M-SCRJ-MM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Installation cut-out



IE-BSS-V14M-SCRJ-MM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Dust caps



For protecting your devices against dust and dirt.

General ordering data

Type	IE-BP-V14P	Version	
Order No.	1058310000	Flange-mounted housing, protective cap	
GTIN (EAN)	4032248799404		
Qty.	10 ST		