

**CB-R 200/7,5 NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**



Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

**General ordering data**

Version	Cable ties, 7.5 x 200 mm, Polyamide 66, 220 N
Order No.	<a href="#">1059200000</a>
Type	CB-R 200/7,5 NC
GTIN (EAN)	4032248806140
Qty.	100 items

## CB-R 200/7,5 NC

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS

Conform

## Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	200 mm	Height (inches)	7.874 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	2.2 g		

## Temperatures

Operating temperature range -40...85 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

## Installation materials

UV-resistant	No	For re-opening	Yes
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	40 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	50 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	3 mm

## Important note

Product information Number of bags in box (pieces): 60  
 Number of items in bag (pieces): 100  
 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.

## Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

**Drawing**

