

CB-R 200/7,5 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

General ordering data

Version	Cable ties, 7.5 x 200 mm, Polyamide 66, 220 N
Order No.	1059200000
Type	CB-R 200/7,5 NC
GTIN (EAN)	4032248806140
Qty.	100 items

CB-R 200/7,5 NC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	200 mm	Height (inches)	7.874 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	2.2 g		

Temperatures

Operating temperature range -40...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	Yes
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	40 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	50 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	3 mm

Important note

Product information Number of bags in box (pieces): 60
 Number of items in bag (pieces): 100
 One delivery unit corresponds to one box quantity, and only multiples of the delivery unit can be ordered.

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

Drawing

