

## CB-R 350/7,5 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

Releasable and reusable cable ties, suitable for temporary bundling and when open-close function is necessary.

### General ordering data

Version	Cable ties, 7.5 x 350 mm, Polyamide 66, 220 N
Order No.	<a href="#">1059250000</a>
Type	CB-R 350/7,5 BK
GTIN (EAN)	4032248806195
Qty.	100 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	2 mm	Depth (inches)	0.0787 inch
Height	350 mm	Height (inches)	13.7795 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	3.98 g		

**Temperatures**

Operating temperature range -40...85 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Installation materials**

UV-resistant	No	For re-opening	Yes
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	100 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	100 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	3.5 mm

**Classifications**

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

**Drawing**

