

SAIL-M12G-CD-5.0B

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, EtherCAT and Ethernet.

General ordering data

| | |
|------------|--|
| Version | Bus line, One end without connector, M12, Number of poles: 5, 5 m, pin, straight, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes |
| Order No. | 1060110500 |
| Type | SAIL-M12G-CD-5.0B |
| GTIN (EAN) | 4032248808885 |
| Qty. | 1 items |

SAIL-M12G-CD-5.0B

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E307231

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Length | 5 mm | Length (inches) | 0.1968 inch |
| Net weight | 346 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1c533b66-fcff-4da5-b89f-fd555bf5cb55 |

Technical specifications for cable

| | | | |
|-----------------------------------|---|--|--------------------------|
| Cable length | 5 m | Sheathing colour | violet |
| Resistance to oils | in accordance with IEC 60811-2-1 | Suitable for cable carriers | No |
| Core cross-section | 0.34 mm ² | Number of wires | 5 |
| Shielded | Yes | Halogen | Yes |
| Insulation | PVC | Acceleration | 7 m/s ² |
| Bending radius, min., stationary | 10 x cable diameter | Bending cycles | 5 Mio |
| Wire cross section (Print/Online) | 2 x 0.34 mm ² + 2 x 0.22 mm ² | Resistance to spread of flame | According to IEC 60754-1 |
| Speed | 180 m/min | Sheath material | PVC |
| Configurable cable length | No | Outer cladding in accordance with UL AWM style | 2571 (80 °C) |
| Hybrid cable | No | Irradiation crosslinked | No |
| Welding spark resistance | No | Colour coding | red, black, white, blue |
| Temperature range, stationary | -40...80 °C | Resistant to welding beads | No |
| Temperature range, moving | -25...80 °C | Number of poles | 5 |
| Outside diameter | 6.7 mm ± 0.3 mm | | |

General technical data

| | | | |
|------------------------------|---------------|------------------------|----------------------|
| Coding | A-coded | Connection thread | M12 |
| Contact surface | Gold-plated | LED | No |
| Version | pin, straight | Housing main material | PUR |
| Contact material | CuZn35PB2 | Nominal voltage | 125 V |
| Nominal current | 4 A | Protection degree | IP67 |
| Plugging cycles jumpered | ≥ 100 | Pollution severity | 3 |
| Temperature range of housing | -25...+80 °C | Threaded ring material | Brass, nickel-plated |
| | | Tightening torque | M12: 0.8 - 1.2 Nm |

Cable specific standards

| | |
|-----------------|---------------------------|
| Poisonous gases | According to EN-50267-2-1 |
|-----------------|---------------------------|

SAIL-M12G-CD-5.0B

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical properties

Nominal voltage 125 V

General standards

Certificate no. (cULus) E307231

Plug, left

Plug left M12, A-coded, Number of poles: 5, IP67, male contact, straight, plug, shielded

Plug, right

Plug right Free conductor end

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |


SAIL-M12G-CD-5.0B

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings


Pole scheme



Male, straight



Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F

