

**IE-CC-V01P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Bayonet plug-in connectors according to IEC  
61076-3-106 ver. 1 (EtherNet/IP), plastic, empty housing

**General ordering data**

Version	Coupling, IP67, Variant 1 to IEC 61076-3-106
Order No.	<a href="#">1061820000</a>
Type	IE-CC-V01P
GTIN (EAN)	4032248811151
Qty.	10 items

## IE-CC-V01P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	118.7 mm	Depth (inches)	4.6732 inch
Height	42.4 mm	Height (inches)	1.6693 inch
Width	41.8 mm	Width (inches)	1.6457 inch
Net weight	5.54 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

UL 94 flammability rating	V-0	Colour	black
Housing main material	PA UL 94 V0	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Protection degree	IP67	Plugging cycles	750

### General standards

Connector standard	IEC 61076-3-106 Var. 1
--------------------	------------------------

### Classifications

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		

**IE-CC-V01P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**

