

IE-OP-V01P-1S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Junction box, design for bayonet plug-in connectors ver.1
according to IEC 61076-3-106, plastic

General ordering data

Version	Wall-mounted junction box, IP67, Variant 1 to IEC 61076-3-106
Order No.	1061830000
Type	IE-OP-V01P-1S
GTIN (EAN)	4032248811182
Qty.	10 items

IE-OP-V01P-1S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	114 mm	Depth (inches)	4.4882 inch
Height	65.2 mm	Height (inches)	2.5669 inch
Width	41.8 mm	Width (inches)	1.6457 inch
Net weight	72 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

UL 94 flammability rating	V-0	Colour	black
Housing main material	PA UL 94 V0	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Protection degree	IP67	Plugging cycles	750

General standards

Connector standard	IEC 61076-3-106 Var. 1
--------------------	------------------------

Classifications

ETIM 8.0	EC002597	ETIM 9.0	EC002597
ETIM 10.0	EC002597	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		

Drawings

Dimensioned drawing

