

WAD 27 NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

General ordering data

Version	Group markers, Cover, 64 x 27 mm, Pitch in mm (P): 27.00 Weidmueller, white
Order No.	1062960000
Type	WAD 27 NE WS
GTIN (EAN)	4008190148225
Qty.	10 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	64 mm	Height (inches)	2.5197 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	4.71 g		

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material	Polyamide 66	Colour	white
UL 94 flammability rating	V-2		

Rating data IECEx/ATEX

Operating temperature range -40...100 °C

Dimensions

Pitch in mm (P) 27.00 mm

General

Operating temperature range, max. 100 °C Operating temperature range, min. -40 °C

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		