

WQV 70/95/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

WQV 70/3 106360



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), when screwed in, Silver grey, 232 A, Number of poles: 3, Pitch in mm (P): 27.00, Insulated: No, Width: 10 mm |
| Order No. | 1063600000 |
| Type | WQV 70/95/3 |
| GTIN (EAN) | 4008190187514 |
| Qty. | 5 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 61.6 mm | Depth (inches) | 2.4252 inch |
| Height | 54 mm | Height (inches) | 2.126 inch |
| Width | 10 mm | Width (inches) | 0.3937 inch |
| Net weight | 159.8 g | | |

Temperatures

| | | | |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|---------------|--------|-------------|
| Basic material | tinned copper | Colour | Silver grey |
|----------------|---------------|--------|-------------|

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | |
|----------------|-----------------|
| Type of fixing | when screwed in |
|----------------|-----------------|

Conductors for clamping (rated connection)

| | |
|-------------------------|------|
| Tightening torque, max. | 3 Nm |
|-------------------------|------|

Dimensions

| | |
|-----------------|----------|
| Pitch in mm (P) | 27.00 mm |
|-----------------|----------|

General

| | |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

Rating data

| | |
|-----------------|-------|
| Nominal current | 232 A |
|-----------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |

Accessories

Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

General ordering data

| | | | |
|------------|---------------------------|---------------------|--|
| Type | WAW 1 NEUTRAL | Version | |
| Order No. | 900450000 | Miscellaneous tools | |
| GTIN (EAN) | 4008190053925 | | |
| Qty. | 1 ST | | |