

WAH 185/300 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Our systems for touch protection ensure greater safety in your cabinet. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Version	Bolt-type screw terminals, Hood, blue, 54 mm
Order No.	1064780000
Type	WAH 185/300 BL
GTIN (EAN)	4008 190103200
Qty.	10 items

WAH 185/300 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	43.9 mm	Depth (inches)	1.7283 inch
Height	139 mm	Height (inches)	5.4724 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	26.98 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Polyamide 66	Colour	blue
UL 94 flammability rating	V-2		

Additional technical data

Type of fixing	Snap-on	Explosion-tested version	No
----------------	---------	--------------------------	----

Dimensions

Pitch in mm (P)	55.00 mm
-----------------	----------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		