

**WZAF 120**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

**General ordering data**

Version	Auxiliary connection (terminal)
Order No.	<a href="#">1066300000</a>
Type	WZAF 120
GTIN (EAN)	4008 190024642
Qty.	10 items

## WZAF 120

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	8.15 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

### System specifications

Version	Additional connection
---------	-----------------------

### Additional technical data

Type of fixing	Snap-on	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

### Dimensions

Pitch in mm (P)	27.00 mm
-----------------	----------

### General

Installation advice	Feed-through (bushing), Direct mounting
---------------------	--

### Rating data

Nominal current	32 A
-----------------	------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-08
ECLASS 15.0	27-25-03-08		