


WSH 1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, Rail support, PA 66 GF 30
Order No.	1068700000
Type	WSH 1
GTIN (EAN)	4008190118389
Qty.	10 items

WSH 1

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	57 mm	Depth (inches)	2.2441 inch
Height	110 mm	Height (inches)	4.3307 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	26.18 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Operating temperature	-50 °C...65 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66 GF 30	Colour	dark beige
UL 94 flammability rating	HB		

System specifications

Version	For the mounting rails	Mounting rail	TS 35
---------	------------------------	---------------	-------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	8.00 mm	Mounting offset	66 mm
-----------------	---------	-----------------	-------

General

Number of poles	1	Installation advice	Direct mounting
Mounting rail	TS 35		

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		