

IE-BP-VAPP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For protecting your devices against dust and dirt.

General ordering data

Version	Flange-mounted housing, protective cap
Order No.	1068930000
Type	IE-BP-VAPP
GTIN (EAN)	4032248823093
Qty.	10 items

IE-BP-VAPP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	19.5 mm	Depth (inches)	0.7677 inch
Net weight	9.68 g		

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

UL 94 flammability rating	V-0	Colour	black
Housing main material	PA UL 94 V0	Type of mounting	Indoors only
Protection degree	IP54		

Classifications

ETIM 8.0	EC002314	ETIM 9.0	EC002314
ETIM 10.0	EC002314	ECLASS 14.0	27-44-02-08
ECLASS 15.0	27-44-02-08		

IE-BP-VAPP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

