

IE-PIC-HYB-S-0,75-300

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

General ordering data

Version	Crimp contact, for plug insert, Hybrid
Order No.	1068950000
Type	IE-PIC-HYB-S-0,75-300
GTIN (EAN)	4032248823109
Qty.	300 items

IE-PIC-HYB-S-0,75-300

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.27 g
------------	--------

Temperatures

Storage temperature	Operating temperature
Installation temperature	

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Shielding	unshielded	Category	Miscellaneous
Wire connection cross section, finely stranded, max.	0.75 mm ²	Wire connection cross section, finely stranded, min.	0.75 mm ²
Connection 2	Crimp		

Electrical properties

Nominal voltage	24 V
-----------------	------

Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing

