

IE-BIC-HYB-P-0,75-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

General ordering data

Version	Crimp contact, for flange insert, Hybrid
Order No.	1068970000
Type	IE-BIC-HYB-P-0,75-300
GTIN (EAN)	4032248823956
Qty.	300 items

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 0.29 g

Temperatures

Storage temperature Installation temperature Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Shielding	unshielded	Category	Miscellaneous
Wire connection cross section, finely stranded, max.	0.75 mm ²	Wire connection cross section, finely stranded, min.	0.75 mm ²
Connection 2	Crimp		

Electrical properties

Nominal voltage 24 V

Important note

Product information Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Dimensioned drawing



IE-BIC-HYB-P-0,75-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Crimping tools



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF HYB	Version	
Order No.	1119580000	Pressing tool, Crimping tool for contacts, 0.08mm ² , 1mm ² ,	
GTIN (EAN)	4032248900626	FoderBcrimp	
Qty.	1 ST		