

Q 10 WDL2.5S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Version	Cross-connector (terminal), when screwed in, yellow, 24 A, Number of poles: 10, Pitch in mm (P): 6.10, Insulated: Yes, Width: 4 mm
Order No.	1071800000
Type	Q 10 WDL2.5S
GTIN (EAN)	4008190424893
Qty.	20 items

Q 10 WDL2.5S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	58.9 mm	Height (inches)	2.3189 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	7.7 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material tinned copper Colour yellow

System specifications

Version For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P) 6.10 mm

General

Number of poles	10	Installation advice	Feed-through (bushing), Direct mounting
-----------------	----	---------------------	--

Rating data

Nominal current 24 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		