

**WAD 4 GE BED****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

|            |   |
|------------|---|
| Version    | Terminal cover, yellow, PA 66, Height: 19.8 mm, Width: 4.5 mm, Depth: 9.6 mm, V-2 |
| Order No.  | <a href="#">1072000000</a>  |
| Type       | WAD 4 GE BED  |
| GTIN (EAN) | 4008190446109   |
| Qty.       | 50 items  |

## WAD 4 GE BED

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 9.6 mm  | Depth (inches)  | 0.378 inch  |
| Height     | 19.8 mm | Height (inches) | 0.7795 inch |
| Width      | 4.5 mm  | Width (inches)  | 0.1772 inch |
| Net weight | 0.24 g  |                 |             |

## Temperatures

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature              | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C        |                                  |        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Basic material            | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-2   |        |        |

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |         |                     |                 |
|--------------------------|---------|---------------------|-----------------|
| Type of fixing           | Snap-on | Installation advice | Direct mounting |
| Explosion-tested version | No      |                     |                 |

## Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 4.00 mm |
|-----------------|---------|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |