

**WBB WDK2.5/BL5.08****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Partition plate (terminal), orange, Height: 58 mm, Width: 5 mm, V-2, PA 66
Order No.	<a href="#">1072660000</a>
Type	WBB WDK2.5/BL5.08
GTIN (EAN)	4008 1904 70555
Qty.	10 items

**WBB WDK2.5/BL5.08**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	45.2 mm	Depth (inches)	1.7795 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	8.5 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	936a8f21-8ce1-4838-a60e-9ad69268c052

**Material data**

Basic material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

**System specifications**

Version	End and intermediate plate
---------	----------------------------

**Additional technical data**

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Classifications**

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		