

Product image



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Version	Cross-connector (terminal), when screwed in, yellow, 24 A, Number of poles: 20, Pitch in mm (P): 6.10, Insulated: Yes, Width: 4 mm
Order No.	1074200000
Type	Q 20 WDL2.5S
GTIN (EAN)	4008 1909 1050 1
Qty.	20 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	119.9 mm	Height (inches)	4.7205 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	15.55 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	tinned copper	Colour	yellow
----------------	---------------	--------	--------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Type of fixing	when screwed in	Installation advice	Feed-through (bushing), Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	6.10 mm
-----------------	---------

General

Number of poles	20	Installation advice	Feed-through (bushing), Direct mounting
-----------------	----	---------------------	--

Rating data

Rated voltage	400 V	Nominal current	24 A
---------------	-------	-----------------	------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		