

## KDSW M20 BN O SC 1 G20

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



The KDSW features a special ring in the shape of a truncated cone. The ring enables connections between cable and lines with single-wire armouring and lead-sheath armouring. This ensures a conductive connection between the cable and the cable gland. In addition, the KDSW comes with two seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to +90°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. When both sealing materials are used, it is possible to achieve IP66 or IP67 protection. The KDSW is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

### General ordering data

Version	KDSW (Klippon double seal SWA Ex cable gland), Cable glands, straight, M 20, 16 mm, Single-wire armouring, 0.9 - 1.25 mm, OD min. 12 - OD max. 17.6 mm, ID min. 6.70 - ID max. 14.00 mm, IP66, IP68 - 2.5 bar, Brass
Order No.	<a href="#">1074520000</a>
Type	KDSW M20 BN O SC 1 G20
GTIN (EAN)	4032248839247
Qty.	20 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00
Alternative product	<a href="#">E1W/20/M20-WM</a>

## KDSW M20 BN O SC 1 G20

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

### Dimensions and weights

Height	58 mm	Height (inches)	2.2835 inch
Length	58 mm	Length (inches)	2.2835 inch
Net weight	186 g		

### Temperatures

Operating temperature	-35 °C...90 °C
-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

### Certificate numbers cable gland

Identification	ATEX: II 2G, Ex db IIC Gb, Ex eb IIC Gb, II 1D, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX 1286X
Approval conditions	ATEX, IECEX		

### General information

Outer cable diameter, max.	17.6 mm	Outer cable diameter, min.	12 mm
Inner cable diameter, max.	14.00 mm	Inner cable diameter, min.	6.70 mm
Protection degree with GWDR	IP66, IP68 - 2.5 bar	Armour, max.	1.25 mm
Armour, min.	0.9 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-35 °C	Pitch of thread	1.5 mm
Halogen	Yes	AF size 1	24 mm
AF size 2	24 mm	Protection degree	IP54
Cable gland	metric, brass	Basic material	Brass
Seal insert	CR	Sealing	CR
External thread	M 20	Length of thread	16 mm
Water depth	25 m (30 Min.)	Type of armouring, short term	SWA
Type of armouring	Single-wire armouring	Installation guidelines	See assembly instructions
Size of protective cap	L30		

### Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04

**KDSW M20 BN O SC 1 G20**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Technical data**

[www.weidmueller.com](http://www.weidmueller.com)

---

ECLASS 15.0

27-14-08-04

---

## KDSW M20 BN O SC 1 G20

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SKMU M20 MS SC	Version	
Order No.	<a href="#">0930640002</a>	SKMU MS (brass locknut), Locknut, M 20, 4 mm, Brass	
GTIN (EAN)	4032248849826		
Qty.	50 ST		

### Safety serrated washer



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	SZS M20	Version	
Order No.	<a href="#">1736310000</a>	SZS (serrated washer), Retaining toothed washers, M 20, Stainless steel 1.4404 (316L)	
GTIN (EAN)	4008190963514		
Qty.	10 ST		

### Earth tags



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

#### General ordering data

Type	EA-RING MS/M20 SC	Version	
Order No.	<a href="#">0930710002</a>	EA (earthing rings), Earthing ring, Miscellaneous, M 20, Brass	
GTIN (EAN)	4032248849819		
Qty.	20 ST		

**KDSW M20 BN O SC 1 G20**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Nylon flat gasket - KSWN**



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	KSWN M20	Version	
Order No.	<a href="#">0930730002</a>	KSWN (flat gasket - nylon), Sealing ring, M 20, Nylon 6	
GTIN (EAN)	4032248849802		
Qty.	25 ST		

**Protective caps**



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	KSP L30	Version	
Order No.	<a href="#">1736580000</a>	KSP (Klippon shroud), Protective cap, PVC	
GTIN (EAN)	4008190956233		
Qty.	10 ST		
Type	KSP L30 S	Version	
Order No.	<a href="#">0930700002</a>	KSP (Klippon shroud), Protective cap, Silicone	
GTIN (EAN)	4032248975976		
Qty.	10 ST		