

KDSW M40 BN L SC 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The KDSW features a special ring in the shape of a truncated cone. The ring enables connections between cable and lines with single-wire armouring and lead-sheath armouring. This ensures a conductive connection between the cable and the cable gland. In addition, the KDSW comes with two seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to +90°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. When both sealing materials are used, it is possible to achieve IP66 or IP67 protection. The KDSW is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

General ordering data

Version	KDSW (Klippon double seal SWA Ex cable gland), Cable glands, straight, M 40, 16 mm, Single-wire armouring, Lead sheath armouring, 1.6 - 2 mm, OD min. 33 - OD max. 40.6 mm, ID min. 25.00 - ID max. 32.20 mm, IP66, IP68 - 2.5 bar, Brass
Order No.	1076370000
Type	KDSW M40 BN L SC 2 G40
GTIN (EAN)	4032248839810
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KDSW M40 BN L SC 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

Dimensions and weights

Height	72 mm	Height (inches)	2.8346 inch
Length	72 mm	Length (inches)	2.8346 inch
Net weight	672 g		

Temperatures

Operating temperature	-35 °C...90 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

Certificate numbers cable gland

Identification	ATEX: II 2G, Ex db IIC Gb, Ex eb IIC Gb, II 1D, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX 1286X
Approval conditions	ATEX, IECEX		

General information

Outer cable diameter, max.	40.6 mm	Outer cable diameter, min.	33 mm
Inner cable diameter, max.	32.20 mm	Inner cable diameter, min.	25.00 mm
Protection degree with GWDR	IP66, IP68 - 2.5 bar	Armour, max.	2 mm
Armour, min.	1.6 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-35 °C	Pitch of thread	1.5 mm
Halogen	Yes	AF size 1	55 mm
AF size 2	55 mm	Protection degree	IP54
Cable gland	metric, brass	Basic material	Brass
Seal insert	CR	Sealing	CR
External thread	M 40	Length of thread	16 mm
Water depth	25 m (30 Min.)	Type of armouring, short term	SWA
Type of armouring	Single-wire armouring, Lead sheath armouring	Installation guidelines	See assembly instructions
Size of protective cap	L55		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04

KDSW M40 BN L SC 2 G40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

ECLASS 15.0

27-14-08-04

KDSW M40 BN L SC 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M40 MS SC	Version	
Order No.	0930640005	SKMU MS (brass locknut), Locknut, M 40, 4.8 mm, Brass	
GTIN (EAN)	4032248976096		
Qty.	10 ST		

Safety serrated washer



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SZS M40	Version	
Order No.	1736340000	SZS (serrated washer), Retaining toothed washers, M 40, Stainless steel 1.4404 (316L)	
GTIN (EAN)	4008190963545		
Qty.	5 ST		

Earth tags



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M40 SC	Version	
Order No.	0930710005	EA (earthing rings), Earthing ring, Miscellaneous, M 40, Brass	
GTIN (EAN)	4032248976201		
Qty.	10 ST		

KDSW M40 BN L SC 2 G40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M40	Version	
Order No.	0899780000	KSWN (flat gasket - nylon), Sealing ring, M 40, Nylon 6	
GTIN (EAN)	4032248850150		
Qty.	25 ST		

Protective caps



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSP L55	Version	
Order No.	1736610000	KSP (Klippon shroud), Protective cap, PVC	
GTIN (EAN)	4008190956271		
Qty.	10 ST		
Type	KSP L55 S	Version	
Order No.	0930700005	KSP (Klippon shroud), Protective cap, Silicone	
GTIN (EAN)	4032248976003		
Qty.	10 ST		